

LSR II H1010

Laser Mirror BP Filter Primary Fluor

Other Suitable Fluors

Violet 405nm 25mW	755 LP	780/60	BV 785/786	Super Bright 780
	690 LP	710/50	BV 711	Super Bright 702
	635 LP	655/20	BV 650	eFluor 650
	600 LP	610/20	BV 605	eFluor 605
	505 LP	525/50	BV 510	Horizon V500, BV 480, L/D Aqua, VioGreen
		450/50	BV 421	eFluor 450, VioBlue, Horizon V450, Pacific Blue, DCV, DAPI, Super Bright 436
Blue 488nm 20mW	635 LP	695/40	PerCP-Cy5.5	PerCP, 7-AAD, PerCP=eFluor 710
	505 LP	525/50	FITC	BB 515, GFP, AF488, VioGreen, CFSE,
		488/10	SSC	
561 nm 100 mW	635 LP(?)	780/60	PE-Cy7	PE-Vio770
	600 LP	610/20	PE-CF594	PE-Texas Red, mCherry, PI, AF594, PE-eFluor 610
		582/15	PE	dsRed, RFP, Cy3, tdTomato
640 nm 40 mW	755 LP	780/60	APC-Cy7	APC-eFluor780.APC-Vio770, APC-H7, L/D Near-IR
	710 LP	730/45	AF 700	
		670/30	APC	AF647